




Belegung Wiring Method



Belegung Wiring Method



- Full HD SVGA Monitorkabel + Audio
- 15 pol. HD Stecker > 15 pol. HD Stecker
- mit 2 Ferrit-Kernen
- mit integrierter 3.5 mm Stereo Audio-Leitung und Adapter
3.5 mm zu 2 x Chinch Audio
- doppelt geschirmt
- AWG 23 + 24
- EAN Code : 4040849939693
- RoHS-konform

- Full HD SVGA Monitor cable + Audio
- 15 pin HD plug > 15 pin HD plug
- with 2 ferrit cores
- with integrated 3.5 mm stereo audio line
and adaptor 3.5 mm to 2 x chinch audio
- double screened
- AWG 23 + 24
- EAN Code : 4040849939693
- RoHS compliant

Änderungen

| Datum | Name | gez.: | Datum | Name | Bezeichnung | Blatt |
|------------|------|--------|------------|------|--------------------------------------|-------|
| 09.11.2011 | tf | gez.: | 18.05.2011 | tf | CAK SVGA XGA 300 15M/15M AUDIO 3m | I |
| | | gepr.: | 18.05.2011 | tf | | |
| | | Norm.: | | | Zeichnungs-Nr.: 93969 | J |
| | | | | | | |

